



- A strong type clamping lever.
- Products of special specifications such as rotating radius of the lever can also be manufactured. Please feel free to contact our customer service.

● Material/Finish

RoHS2 Compliant

	LTF
Lever Part	S45C Ferrosferric Oxide Film (Black)
Thread Part	S45C Ferrosferric Oxide Film (Black)
Grip	Phenol Resin (Black)

Unit : mm

Part Number	M (Coarse)		Lf	R	H	H'	h	s	A	B	D	d	Number of Teeth	Max. load*1 (N)	Max. clamping*1 force (kN)	Mass (g)
	Nominal of Thread	Pitch														
LTF-10	M10	1.5	23	81	72.5	78	42.5	2.5	10	25	24	17	24	280	16	170
LTF-12	M12	1.75	26	99	85.5	92	49.5	3.5	11	25	28	20	26	400	23	270
LTF-16	M16	2	30	118	98.5	106	55.5	3.5	12	30	33	24	36	830	43	405
LTF-20	M20	2.5	35	136	114.5	123	65.5	4.5	14	35	41	30	36	1400	67	705

*1: About the definition of max. load / max. clamping force → P.xxxx

● Related Products

Male screw type tension lever

LTM is available.

→ P.xxxx



● Part number specification

LTF-20



Cleanroom Wash & Packaging → P.xxxx	Screw Combination → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx
Not Available	Not Available	Not Available	Not Available	Available / Add'l charge