



- All stainless steel grip superior in corrosion resistance and strength

- Material/Finish

RoHS2 Compliant

	GSS
Main body	SUS304

Unit : mm

Part Number	D	M (Coarse)		Lm	d	H	h	h ₁	Mass (g)
		Nominal of Thread	Pitch						
GSS-5	10	M5	0.8	6	8	40	30	10	25
GSS-6	13	M6	1	7	10	50	37	13	50
GSS-8	16	M8	1.25	8	12	64	49	15	100
GSS-10	20	M10	1.5	10	15	70	50	20	150
GSS-12	25	M12	1.75	13	18	100	70	30	370

- Usage example

In combination with a stainless steel handwheel

HSM (→ P.xxxx).



- Part number specification

GSS-5



Cleanroom Wash & Packaging → P.xxxx

Vibration Resistant → P.xxxx

Laser Marking → P.xxxx

Modification of Shaft Hole Diameter → P.xxxx

Available / Add'l charge

Available / Add'l charge

Available / Add'l charge

Not Available