



- **KNWFS-A4** (SCS14製)と**KNWFS** (SCS13製)を区別するため、**KNWFS-A4**は底面に溝加工を施しています。

- 材質・仕上げ



| | KNWFS-A4 |
|----|-----------------------------|
| 本体 | SCS14(SUS316相当) ショットブラスト |

単位：mm

| 品番  | D | M(並目) | | Lf min. | H | s | B | d | 質量(g) |
|--|----|-------|------|---------|------|-----|----|----|-------|
| | | ねじの呼び | ピッチ | | | | | | |
| KNWFS-20-M4-A4 | 20 | M4 | 0.7 | 7 | 11.5 | 3.5 | 9 | 8 | 10 |
| KNWFS-26-M4-A4 | 26 | M4 | 0.7 | 7 | 14.5 | 4.5 | 11 | 10 | 20 |
| KNWFS-26-M5-A4 | 26 | M5 | 0.8 | 8 | 14.5 | 4.5 | 11 | 10 | 19 |
| KNWFS-26-M6-A4 | 26 | M6 | 1 | 8 | 14.5 | 4.5 | 11 | 10 | 18 |
| KNWFS-34-M6-A4 | 34 | M6 | 1 | 10 | 17 | 5 | 13 | 12 | 35 |
| KNWFS-34-M8-A4 | 34 | M8 | 1.25 | 9 | 17 | 5 | 13 | 12 | 33 |

- 品番指定 ※価格・納期はNBKウェブサイトをご覧ください。

KNWFS-26-M5-A4

| | | | | |
|---|---|---|---|---|
|  クリーン洗浄・クリーン梱包 → P. xxxx |  ねじ組み合わせ → P. xxxx |  ねじカット → P. xxxx |  ゆるみ止め → P. xxxx |  レーザ刻印 → P. xxxx |
| お問い合わせください | 対応可・別料金 | 対応不可 | 対応不可 | 対応可・別料金 |