




SPE-R Plastic Screws - Hex Socket Head Cap Screw Plugs - PEEK

Heat-resistance Chemical-proof



- PEEK is a thermoplastic super-engineering plastic with excellent physical and chemical properties.
- These screws have excellent chemical resistance. They are mostly unaffected by chemicals excluding concentrate sulfuric acid, concentrate nitric acid, and concentrate hydrofluoric acid.
- These screws have excellent heat resistance, water resistance, and high heat resistance strength.
- These screws have excellent abrasion, shock, and fatigue resistance.
- They have high incombustibility that meets V-0 of UL 94.
- The properties and precautions of plastic screws → P.xxxx

• Application

FPD production equipment, semiconductor devices, printed circuit board etching devices, metallic surface treatment equipment and facilities, chemical plants, transformers, electrical and electronic equipment, hot water pumps, and chemical pumps

• Material/Finish



	SPE-R
Main body	PEEK/Light Brown
Heat Resistance Temperature*1	260°C

*1 : This is the value for the plastic material. The maximum operating temperature of the product changes with performance conditions such as tightening torque.

Unit : mm

Part Number	R (PT) Nominal of Thread	L	B	Mass (g)	Qty per Pack
SPE-1-R	R1/8	8	5	0.45	5
SPE-2-R	R1/4	11	6	1.1	5
SPE-3-R	R3/8	12	8	2.1	5

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

• Part number specification

SPE-2-R



Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available