


SNFXS Hexalobular Socket Flat Head Machine Screws

SUS Stainless steel  Protrusion



● Application

Prevention of damage to screw heads and reliable tightening

● Material/Finish



	SNFXS
Main Body	SUSXM7 (Equivalent to SUS304)
Strength Class	A2-50

● Part number specification

SNFXS-M5 - 20



- Hexalobular socket shapes*1 are designed to withstand high tightening torque compared to cross-recesses. → P.xxxx
- Screw heads are unlikely to be damaged due to tightening, allowing safe and secure tightening to be performed.
- Mounting/removing with regular tools such as hex keys and screwdrivers is not possible. Also usable for applications including prevention of disassembly, theft, or tampering for devices or facilities.* 2
- Install and remove with **SKX** Dedicated Wrench or **SKXB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.
- Use the **SKX-N** hexalobular wrench for extremely limited access spaces for mounting and removing in tight spaces.

*1 : The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

*2 : Tools for hexalobular sockets are commercially available. When tampering prevention is the main objective, consider tamper resistant screws. → P.xxxx

Unit : mm

Part Number	M (Coarse)		L	D1	L1	Applicable wrench	Hexalobular Socket No.	t	Mass (g)	Qty per pack
	Nominal of Thread	Pitch								
SNFXS-M2	M2	0.4	4 5 6 8 10 12	3.8	1.2	SKX-6	6	0.64	0.14 - 0.29	20
SNFXS-M2.5	M2.5	0.45	4 5 6 8 10 12 16	4.7	1.5	SKX-8	8	0.79	0.27 - 0.65	20
SNFXS-M3	M3	0.5	5 6 8 10 12 16 20	5.5	1.65	SKX-10	10	0.83	0.49 - 1.1	20
SNFXS-M4	M4	0.7	6 8 10 12 16 20 25	8.4	2.7	SKX-20	20	1.53	1 - 2.5	20
SNFXS-M5	M5	0.8	8 10 12 16 20 25 30	9.3	2.7	SKX-25	25	1.51	2.2 - 4.8	20
SNFXS-M6	M6	1	10 12 16 20 25 30	11.3	3.3	SKX-30	30	1.78	3.9 - 7.4	20

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Related Products

SKX Hexalobular Wrench



SKXB Hexalobular Short Bit



SKX-N Hexalobular Wrench for Extremely Limited Access Spaces



SRD Magnet Screwdriver



Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available