




SNSS-M-P Hex Socket Head Cap Screws - Fine Pitch Thread

SUS Stainless steel



- Conforms to JIS B 1176, ISO 12474, and DIN 912.
- Socket head cap screws with fine pitch thread.
- The effective diameter is larger and fatigue strength is better than coarse threads.
- The thread pitch is small and the number of thread peaks is more than coarse threads. For securing for cases where a which coarse thread screws lack sufficient thread peaks.
- Since the lead angle of the thread peak is smaller than that of coarse threads, there is little slippage of the thread peak surface, which prevents screws from loosening.

• Application

Loosening prevention
Securement of thin plates, etc.

• Material/Finish




	SNSS
Main Body	SUSXM7 (Equivalent to SUS304)
Strength Class	A2-50 (M4 - M6) A2-70 (M8 - M12)

Unit : mm

Part Number ◀1	M (Fine)		L ◀2												D1	L1	B	Mass (g)
	Nominal of Thread	Pitch	8	10	12	15	20	25	30	35	40	45	50					
SNSS-M4-P0.5	M4	0.5	8	10	12	15	20	25							7	4	3	1.7 - 3.2
SNSS-M5-P0.5	M5	0.5		10	12	15	20	25	30						8.5	5	4	2.7 - 5.6
SNSS-M6-P0.75	M6	0.75	8	10	12	15	20	25	30						10	6	5	4.3 - 8.3
SNSS-M8-P1	M8	1			12	15	20	25	30	35	40	45	50		13	8	6	11 - 25
SNSS-M10-P1	M10	1				15	20	25	30	35	40	45	50		16	10	8	21 - 39
SNSS-M12-P1	M12	1					20	25	30	35	40	45	50		18	12	10	32 - 55

• Part number specification

SNSS-M5-P0.5-20



1 Individual Sales 1 piece in 1 pack	Cleanroom Wash & Packaging Available / Add'l charge	Screw Length Adjustment Available / Add'l charge	Vibration Resistant Available / Add'l charge	Modification process for captive use Available / Add'l charge
--	--	---	---	--