


# SLP Hex Socket Head Cap Screws with Low Profile with Pilot Recess



- Hex socket head cap screw with low head.
- For space-saving of equipment/devices and applications with limited overhead space.
- Use a dedicated wrench **SKP** for mounting and removing. As the pilot recess guides securely, you can tighten at higher torque more safely. (Commercially available hex keys can also be used for tightening.)

### ● Application

Reducing the size of equipment and devices

### ● Material/Finish




	<b>SLP</b>
Main Body	Equivalent to S45C Ferrosferric Oxide Film (Black)
Strength Class	8.8

Unit : mm

Part Number <span style="color:red">❶</span>	M (Coarse)		L <span style="color:red">❷</span>	D1	L1	B	t	Lb	Max. Torque (N·m)	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch									
<b>SLP-M4</b>	M4	0.7	8	7	2.8	3	1.6	3.5	2	1.3 - 1.4	20
<b>SLP-M5</b>	M5	0.8	10	8.5	3.5	4	2	4.2	6	2 - 3.3	20
<b>SLP-M6</b>	M6	1	10	10	4	5	2.5	5.5	9	3.5 - 5.3	20
<b>SLP-M8</b>	M8	1.25	12	13	5	6	3	7	20	7.8 - 10	20

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

### ● Dedicated Wrench



Unit : mm

Part Number	B Nominal of Width Across Flats	L1	L2	Applicable Screw	Mass (g)
<b>SKP-3</b>	3	63	20	SLP-M4	5
<b>SKP-4</b>	4	71	25	SLP-M5	10
<b>SKP-5</b>	5	80	28	SLP-M6	28
<b>SKP-6</b>	6	90	32	SLP-M8	34

### ● Part number specification

**SLP-M6-20**



<b>Individual Sales</b> → P.0000	<b>Cleanroom Wash &amp; Packaging</b> → P.0000	<b>Screw Length Adjustment</b> → P.0000	<b>Vibration Resistant</b> → P.0000	<b>Modification process for captive use</b> → P.0000
Available / Add'l charge	Not Available	Available / Add'l charge	Available / Add'l charge	Not Available