




# SFT/SFTS Hex Socket Pipe Plugs

**SUS** Stainless steel



- Sinking type Pipe Taper Screw Plugs
- **SFT-PS** and **SFTS-PS** are pre-coated seal types which do not require sealing tape or sealant. This dramatically reduces work time. The sealing effect is also excellent.
- Pre-coated seals have excellent resistance to oil, gasoline, water, and heat.
- Application

Hydraulic equipment, pneumatic machinery and equipment, and general industrial machines

## ● Material/Finish



	SFT	SFT-PS	SFTS	SFTS-PS
Main Body	S45C (Hardness: 32 - 42 HRC) Ferrosoferric Oxide Film (Black)	S45C (Hardness: 32 - 42 HRC) Ferrosoferric Oxide Film (Black)	SUSXM7 (Equivalent to SUS304)	SUSXM7 (Equivalent to SUS304)

## SFT SFT-PS Steel · Ferrosoferric Oxide Coating

Unit : mm

SFT No Seal	SFT-PS Pre-coat Seal	Common dimensions							Qty per pack
Part Number ◀1	Part Number ◀1	R (PT) Nominal of Thread	D1*1	k	L	B	t	Mass (g)	
<b>SFT-0.5</b>	<b>SFT-0.5-PS</b>	R1/16	7.723	0.45	6	4	3	2	10
<b>SFT-1</b>	<b>SFT-1-PS</b>	R1/8	9.728	0.45	7	5	3.5	3	10
<b>SFT-2</b>	<b>SFT-2-PS</b>	R1/4	13.157	0.7	8.9	6	4.5	6	10
<b>SFT-3</b>	<b>SFT-3-PS</b>	R3/8	16.662	0.7	10	8	5	11	10
<b>SFT-4</b>	<b>SFT-4-PS</b>	R1/2	20.955	0.9	12	10	6	21	5

\*1: The D1 dimension is a reference value (theoretical value).

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

## SFTS SFTS-PS Stainless Steel

Unit : mm

SFTS No Seal	SFTS-PS Pre-coat Seal	Common dimensions							Mass (g)
Part Number ◀1	Part Number ◀1	R (PT) Nominal of Thread	D1*1	k	L	B	t		
<b>SFTS-0.5</b>	<b>SFTS-0.5-PS</b>	R1/16	7.723	0.45	6	4	3	2	
<b>SFTS-1</b>	<b>SFTS-1-PS</b>	R1/8	9.728	0.45	7	5	3.5	3	
<b>SFTS-2</b>	<b>SFTS-2-PS</b>	R1/4	13.157	0.7	8.9	6	4.5	6	
<b>SFTS-3</b>	<b>SFTS-3-PS</b>	R3/8	16.662	0.7	10	8	5	11	
<b>SFTS-4</b>	<b>SFTS-4-PS</b>	R1/2	20.955	0.9	12	10	6	21	

## ● Part number specification

### SFT-3-PS



Cleanroom Wash and Packaging service is only available for **SFTS** at an extra charge.

<b>1</b> Individual Sales → P.0000	<b>2</b> Cleanroom Wash & Packaging → P.0000	<b>3</b> Screw Length Adjustment → P.0000	<b>4</b> Vibration Resistant → P.0000	<b>5</b> Modification process for captive use → P.0000
Available / Add'l charge	Partially Available / Add'l charge	Not Available	Not Available	Not Available