


# SAD-FT / SADS-FT Screw Adaptors - Long Threaded Type



SUS Stainless steel



- By combining with female screw products such as a lever and knob, this may be used as a long screw lever or knob.
- For screw fixing, use a pin stopper or anaerobic adhesive agent.
- If it is repeatedly tightened in combination with a lever or knob, a pin stopper is recommended.

• Material/Finish **1**



	<b>SAD-FT</b> Made of Steel	<b>SADS-FT</b> Made of Stainless Steel
Thread	SWRM6K	SUS304
Part	Trivalent Chromate Treatment	

## Dimensions

Part Number Made of Steel	Part Number Made of Stainless Steel	M (Coarse)		Mass (g)
		Nominal of Thread <b>2</b>	Pitch	
<b>SAD-M4-FT</b>	<b>SADS-M4-FT</b>	M4	0.7	4 - 10
<b>SAD-M5-FT</b>	<b>SADS-M5-FT</b>	M5	0.8	6.2 - 16
<b>SAD-M6-FT</b>	<b>SADS-M6-FT</b>	M6	1	11 - 22
<b>SAD-M8-FT</b>	<b>SADS-M8-FT</b>	M8	1.25	20 - 40
<b>SAD-M10-FT</b>	<b>SADS-M10-FT</b>	M10	1.5	36 - 72

**SAD-FT** Made of Steel    **SADS-FT** Made of Stainless Steel

Part Number	L (mm) <b>3</b>					
	40	50	60	80	100	120
<b>SAD-M4-FT</b>	●	●	●	●	●	
<b>SAD-M5-FT</b>	●	●	●	●	●	
<b>SAD-M6-FT</b>		●	●	●	●	
<b>SAD-M8-FT</b>		●	●	●	●	
<b>SAD-M10-FT</b>			●	●	●	●
<b>SADS-M4-FT</b>	●	●	●	●	●	
<b>SADS-M5-FT</b>	●	●	●	●	●	
<b>SADS-M6-FT</b>		●	●	●	●	
<b>SADS-M8-FT</b>		●	●	●	●	
<b>SADS-M10-FT</b>			●	●	●	●

• Part number specification

**SAD-M5-100-FT**

**1**    **2**    **3**    Long Threaded Type

Cleanroom Wash & Packaging → P.0000	Screw Combination → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000
S.S. only / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge