



- Clamping screw with an integral special ball (full ball type).
- Point contact by full ball securely fixes a work.
- For tool holder set screw, pressure piece and stopper.
- We also produce products of special specifications, e.g. nominal diameter of thread, length and surface treatment. Please feel free to contact our customer service.

• Material/Finish



	SCS-BR Brass Ball
Thread Part	SCM435 Ferrosferric Oxide Film (Black)
Ball	Brass

Unit : mm

Part Number	M (Coarse)		L	D	B	Mass (g)
	Nominal of Thread	Pitch				
SCS-M4-6-BR	M4	0.7	6.5	2	2	0.4
SCS-M4-10-BR	M4	0.7	10.5	2	2	0.7
SCS-M4-16-BR	M4	0.7	16.5	2	2	1
SCS-M5-8-BR	M5	0.8	8.6	3	2.5	0.8
SCS-M5-12-BR	M5	0.8	12.6	3	2.5	1.3
SCS-M5-20-BR	M5	0.8	20.6	3	2.5	2.3
SCS-M6-10-BR	M6	1	10.8	4	3	1.5
SCS-M6-16-BR	M6	1	16.8	4	3	2.5
SCS-M6-20-BR	M6	1	20.8	4	3	3.4
SCS-M6-25-BR	M6	1	25.8	4	3	4

• Part Number Specification

SCS-M4-6-BR



Cleanroom Wash & Packaging	Screw Combination	Screw Length Adjustment	Vibration Resistant
Please feel free to contact us	Available / Add'l charge	Not Available	Available / Add'l charge