




SWALG-F Plain Washers for High Strength Stainless Steel Bolts

Heat-resistance
 Chemical-proof
 Non-Magnetic
 SUS Stainless steel



● Material/Finish



RoHS

	SWALG-F
Main Body	SUS316L (Hardness: 300 - 400 HV)



- Plain washers for high strength stainless steel bolts.
- Hardness is 300 HV or higher. Even higher hardness than general stainless steel plain washers.
- Suited to use with stainless steel bolts of tensile strength 800 N/mm² to 1000 N/mm². *1
Use in combination with high strength stainless steel hex socket head cap screws **SNSLG** (→ P.xxxx) or **SNSX** (→ P.xxxx).
- Made of SUS316L. It has excellent corrosion resistance.

*1: JIS B 1256 "Plain washers" regulates plain washer hardness categories and applicable fasteners.

● Application

FPD production equipment / Semiconductor manufacturing equipment / Equipment and device structures / Nitric acid plants / Offshore instruments / General industrial machines

Unit : mm

Part Number	Nominal	d	D	t	Mass (g)	Qty per Pack
SWALG-3-F	3	3.2	7	0.5	0.11	10
SWALG-4-F	4	4.3	9	0.8	0.27	10
SWALG-5-F	5	5.3	10	1	0.4	10
SWALG-6-F	6	6.4	12	1.6	0.91	10

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part number specification

SWALG-3-F



Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available