


SRBS Button Head Cap Screws with Hexalobular Socket and Pin

SUS Stainless steel Tamper Resistance



● Material/Finish



	SRBS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

- Button head cap screws with a pin at the center of the hexalobular socket *1.
- This prevents mounting and removing with regular tools.
- Install and remove with **SRX** Dedicated Wrench or **SRXB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.

*1: The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

● Application

Equipment/devices disassembly/tampering prevention
Theft prevention for outdoor facilities
Security measures
Safety measures

Part Number	M (Coarse)		L												D1	L1	Applicable Wrench Type	Applicable Bit Type		Hexalobular Socket No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch	6	8	10	12	15	16	20	25	30	35	40	Bit				Driver				
SRBS-M3	M3	0.5	6	8	10	12	15	16	20	25					5.7	1.65	SRX-10	SRXB-10	SRD-6.35	10	0.48 - 1.4	20
SRBS-M4	M4	0.7	6	8	10	12	15	16	20	25	30	35	40		7.6	2.2	SRX-20	SRXB-20	SRD-6.35	20	1.1 - 4.2	20*1
SRBS-M5	M5	0.8		8	10	12	15	16	20	25	30		40		9.5	2.75	SRX-25	SRXB-25	SRD-6.35	25	1.8 - 6.4	20
SRBS-M6	M6	1		8	10	12	15	16	20	25	30		40	50	10.5	3.3	SRX-30	SRXB-30	SRD-6.35	30	3 - 12	10
SRBS-M8	M8	1.25			10	12		16	20	25	30		40	50	14	4.4	SRX-40	SRXB-40	SRD-6.35	40	7.3 - 22	10


*1: Quantity per pack for **SRBS-M4-35** and **SRBS-M4-40** is 1.

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● **SRX** Dedicated Wrench


Unit : mm

Part Number	L1	L2	Mass (g)
SRX-10	60	20	3.7
SRX-20	67	23	8.2
SRX-25	70	25	11
SRX-30	81	28	20
SRX-40	88	31	32



● **SRXB** Bit Part No.


Part Number	Mass (g)
SRXB-10	4.36
SRXB-20	4.57
SRXB-25	4.79
SRXB-30	5.50
SRXB-40	6.00



● **SRD** Dedicated Magnet Screwdriver

Unit : mm

Part Number	L	B	Mass (g)
SRD-6.35	210	6.35	98



● Part Number Specification

SRBS-M5-16



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge