




SRWS Triwing Pan Head Machine Screws

Tamper Resistance **SUS** Stainless steel



- This prevents mounting and removing with regular tools.
- Install and remove with **SRWB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.

Application

Machinery / Tools / Equipment / Devices disassembly prevention / Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

Material/Finish



SRWS	
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

Unit : mm

Part Number 1	M (Coarse)		L 2				D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)	Qty per Pack	
	Nominal of Thread	Pitch											
SRWS-M3	M3	0.5	6	8	10		5.6	1.8	SRWB-2	SRD-6.35	0.54 - 0.7	20	
SRWS-M4	M4	0.7		8	10	12	8.2	2.9	SRWB-4	SRD-6.35	1.5 - 1.9	20	
SRWS-M5	M5	0.8			10	12	16	9.5	3.4	SRWB-5	SRD-6.35	2.8 - 3.5	20

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

SRWB Dedicated Bit

Unit : mm

Part Number	L	B	Mass (g)
SRWB-2	25.4	6.35	4.8
SRWB-4	25.4	6.35	5.2
SRWB-5	25.4	6.35	5.6

SRWB




SRD Dedicated Magnet Screwdriver

Unit : mm

Part Number	L	B	Mass (g)
SRD-6.35	210	6.35	98

SRD



Part number specification

SRWS-M5-16



1 Individual Sales → P.0000	2 Cleanroom Wash & Packaging → P.0000	3 Screw Length Adjustment → P.0000	4 Vibration Resistant → P.0000	5 Modification process for captive use → P.0000
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge