



- The grip is made of phenol resin. It is highly durable.
- There are two types of the lever part material. **1**

LRG — Made of steel

LRGS — Made of stainless steel

- Material/Finish



	LRG	LRGS
Lever Part	Steel Matte Chrome Plating	SUS303
Grip	Phenol Resin (Black)	Phenol Resin (Black)

Unit : mm

Part Number <small>Lever : Steel</small>	Part Number <small>Lever : Stainless steel</small>	M (Coarse)		Lm	L 3	A	B	G	Mass (g)
		Nominal of Thread 2	Pitch						
LRG-6-63	LRGS-6-63	M6	1	12	63	8	17	38	25
LRG-6-80	LRGS-6-80	M6	1	12	80	8	17	38	32
LRG-6-100	LRGS-6-100	M6	1	12	100	8	17	38	40
LRG-8-80	LRGS-8-80	M8	1.25	20	80	10	21	50	53
LRG-8-100	LRGS-8-100	M8	1.25	20	100	10	21	50	65
LRG-8-125	LRGS-8-125	M8	1.25	20	125	10	21	50	81
LRG-10-100	LRGS-10-100	M10	1.5	25	100	12	25	65	97
LRG-10-125	LRGS-10-125	M10	1.5	25	125	12	25	65	119
LRG-10-160	LRGS-10-160	M10	1.5	25	160	12	25	65	149
LRG-12-125	LRGS-12-125	M12	1.75	30	125	14	28	85	163
LRG-12-160	LRGS-12-160	M12	1.75	30	160	14	28	85	205
LRG-12-200	LRGS-12-200	M12	1.75	30	200	14	28	85	253

- Part number specification

LRG-6-63



Cleanroom Wash & Packaging → P.xxxxx	Screw Combination → P.xxxxx	Screw Length Adjustment → P.xxxxx	Vibration Resistant → P.xxxxx	Laser Marking → P.xxxxx
Please feel free to contact us	Not Available	Not Available	Available / Add'l charge	Available / Add'l charge