



GNTR



GNTRS

- Back mounting method with hexagon socket
- The thread parts made of steel and stainless steel are standardized.
- Material/Finish



	GNTR Thread Part: Made of Steel	GNTRS Thread Part: Made of Stainless Steel
Grip Part	Nylon 6 (Black)	Nylon 6 (Black)
Thread Part	SS400 Trivalent Chromate Treatment	SUS303

Unit : mm

Part Number Screw : Steel	Part Number Screw : Stainless	D	M (Coarse)		Lm	d	d1	H	h	B	Mass (g)
			Nominal of Thread	Pitch							
GNTR-18-M5	GNTRS-18-M5	18	M5	0.8	10	12	6.5	51	50	2.5	23
GNTR-19-M6	GNTRS-19-M6	19	M6	1	13	13	8	66	65	3	40
GNTR-24-M8	GNTRS-24-M8	24	M8	1.25	16	17	10.3	81	80	4	84
GNTR-28-M10	GNTRS-28-M10	28	M10	1.5	18	20	13	96	95	5	141

- Part number specification

GNTRS-28-M10



Cleanroom Wash & Packaging → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx	Modification of Shaft Hole Diameter → P.xxxx
Not Available	Available / Add'l charge	Available / Add'l charge	Not Available