



- Use it in combination with stepped locating pin **PJP** ( → P.xxxx).

- Material/Finish



	<b>PJA</b>
Main body	Steel (hardness: 60 HRC or above)

Unit : mm

Part Number	d <b>1</b>	L <b>2</b>						D	R	Applicable positioning pin <b>PJP</b> → P.xxxx	Mass (g)
<b>PJA-5</b>	5	8	10	12	16			10	1	PJP-5-***	3.8 - 7.5
<b>PJA-6</b>	6	8	10	12	16			10	1	PJP-6-***	3.2 - 6.4
<b>PJA-8</b>	8		10	12	16	20		12	2	PJP-8-***	5 - 10
<b>PJA-10</b>	10		10	12	16	20		15	2	PJP-10-***	7.8 - 16
<b>PJA-12</b>	12				16	20	25	18	2	PJP-12-***	19 - 28

- Part number specification

**PJA-5-12**

Product Code **1 2**

Cleanroom Wash & Packaging → P.xxxx  
Not Available

Vibration Resistant → P.xxxx  
Not Available

Laser Marking → P.xxxx  
Not Available