



- Split type set collars.
- Because the shaft hole part can be fully split, mounting and removal are easy, with no damage to the shaft.
- Optimal for use with machines and devices that are difficult to disassemble.



• Material/Finish



	NSCSS-C	NSCSS-M	NSCSS-S
Main Body	S45C Ferrosoferric Oxide Film (Black)	S45C Electroless Nickel Plating	SUS304
Hex Socket Head Cap Screw	SCM435 Ferrosoferric Oxide Film (Black)	SUSXM7	SUSXM7

NSCSS-C Made of Steel, Ferrosoferric Oxide Film NSCSS-M Made of Steel, Electroless Nickel Plating NSCSS-S Made of Stainless Steel

Part Number	Part Number	Part Number	d	B	D	F	M (Coarse)*1	Mass (g)
NSCSS-3-8-C	NSCSS-3-8-M	NSCSS-3-8-S	3	8	15	4.5	M3	9
NSCSS-4-8-C	NSCSS-4-8-M	NSCSS-4-8-S	4	8	15	4.5	M3	7
NSCSS-5-6-C	NSCSS-5-6-M	NSCSS-5-6-S	5	6	16	5	M2.6	7
NSCSS-5-8-C	NSCSS-5-8-M	NSCSS-5-8-S	5	8	20	5.5	M3	14
NSCSS-5-10-C	NSCSS-5-10-M	NSCSS-5-10-S	5	10	20	6	M4	20
NSCSS-6-6-C	NSCSS-6-6-M	NSCSS-6-6-S	6	6	18	6	M2.6	9
NSCSS-6-8-C	NSCSS-6-8-M	NSCSS-6-8-S	6	8	20	6	M3	15
NSCSS-6-10-C	NSCSS-6-10-M	NSCSS-6-10-S	6	10	20	6	M4	19
NSCSS-8-6-C	NSCSS-8-6-M	NSCSS-8-6-S	8	6	22	7	M2.6	13
NSCSS-8-8-C	NSCSS-8-8-M	NSCSS-8-8-S	8	8	25	8	M3	24
NSCSS-8-10-C	NSCSS-8-10-M	NSCSS-8-10-S	8	10	25	8	M4	30
NSCSS-8-12-C	NSCSS-8-12-M	NSCSS-8-12-S	8	12	28	8.5	M5	47
NSCSS-8-15-C	NSCSS-8-15-M	NSCSS-8-15-S	8	15	30	9	M6	63
NSCSS-10-6-C	NSCSS-10-6-M	NSCSS-10-6-S	10	6	25	8	M2.6	16
NSCSS-10-10-C	NSCSS-10-10-M	NSCSS-10-10-S	10	10	30	9	M4	41
NSCSS-10-12-C	NSCSS-10-12-M	NSCSS-10-12-S	10	12	30	9	M5	51
NSCSS-10-15-C	NSCSS-10-15-M	NSCSS-10-15-S	10	15	35	10	M6	86
NSCSS-12-6-C	NSCSS-12-6-M	NSCSS-12-6-S	12	6	25	9	M2.6	15
NSCSS-12-10-C	NSCSS-12-10-M	NSCSS-12-10-S	12	10	30	10	M4	40
NSCSS-12-12-C	NSCSS-12-12-M	NSCSS-12-12-S	12	12	30	10	M5	49
NSCSS-12-15-C	NSCSS-12-15-M	NSCSS-12-15-S	12	15	35	11	M6	84
NSCSS-13-8-C	NSCSS-13-8-M	NSCSS-13-8-S	13	8	28	11	M3	26
NSCSS-13-10-C	NSCSS-13-10-M	NSCSS-13-10-S	13	10	30	10	M4	38
NSCSS-13-15-C	NSCSS-13-15-M	NSCSS-13-15-S	13	15	35	11	M6	80
NSCSS-15-8-C	NSCSS-15-8-M	NSCSS-15-8-S	15	8	30	11	M3	28
NSCSS-15-10-C	NSCSS-15-10-M	NSCSS-15-10-S	15	10	32	11	M4	42
NSCSS-15-12-C	NSCSS-15-12-M	NSCSS-15-12-S	15	12	35	12	M5	64
NSCSS-15-15-C	NSCSS-15-15-M	NSCSS-15-15-S	15	15	40	13	M6	109

*1: Hex socket head cap screw is provided.

Part Number	Part Number	Part Number	d	B	D	F	M (Coarse)*1	Mass (g)
NSCSS-16-8-C	NSCSS-16-8-M	NSCSS-16-8-S	16	8	30	11.5	M3	27
NSCSS-16-10-C	NSCSS-16-10-M	NSCSS-16-10-S	16	10	35	12	M4	51
NSCSS-16-12-C	NSCSS-16-12-M	NSCSS-16-12-S	16	12	35	12	M5	62
NSCSS-16-15-C	NSCSS-16-15-M	NSCSS-16-15-S	16	15	40	13	M6	107
NSCSS-17-15-C	NSCSS-17-15-M	NSCSS-17-15-S	17	15	40	13	M6	106
NSCSS-18-15-C	NSCSS-18-15-M	NSCSS-18-15-S	18	15	45	15	M6	136
NSCSS-20-8-C	NSCSS-20-8-M	NSCSS-20-8-S	20	8	35	13	M3	35
NSCSS-20-10-C	NSCSS-20-10-M	NSCSS-20-10-S	20	10	40	14	M4	65
NSCSS-20-12-C	NSCSS-20-12-M	NSCSS-20-12-S	20	12	40	14	M5	77
NSCSS-20-15-C	NSCSS-20-15-M	NSCSS-20-15-S	20	15	45	15	M6	131
NSCSS-25-10-C	NSCSS-25-10-M	NSCSS-25-10-S	25	10	42	16.5	M4	62
NSCSS-25-12-C	NSCSS-25-12-M	NSCSS-25-12-S	25	12	45	17	M5	92
NSCSS-25-15-C	NSCSS-25-15-M	NSCSS-25-15-S	25	15	50	18	M6	152
NSCSS-30-12-C	NSCSS-30-12-M	NSCSS-30-12-S	30	12	50	20	M5	106
NSCSS-30-15-C	NSCSS-30-15-M	NSCSS-30-15-S	30	15	55	20	M6	171
NSCSS-35-12-C	NSCSS-35-12-M	NSCSS-35-12-S	35	12	55	22.5	M5	118
NSCSS-35-15-C	NSCSS-35-15-M	NSCSS-35-15-S	35	15	60	23	M6	195
NSCSS-40-12-C	NSCSS-40-12-M	NSCSS-40-12-S	40	12	60	25	M5	131
NSCSS-40-18-C	NSCSS-40-18-M	NSCSS-40-18-S	40	18	70	26	M8	334
NSCSS-45-12-C	NSCSS-45-12-M	NSCSS-45-12-S	45	12	65	28	M5	148
NSCSS-45-18-C	NSCSS-45-18-M	NSCSS-45-18-S	45	18	75	28	M8	356
NSCSS-50-15-C	NSCSS-50-15-M	NSCSS-50-15-S	50	15	75	30.5	M6	258
NSCSS-50-18-C	NSCSS-50-18-M	NSCSS-50-18-S	50	18	80	32	M8	393
NSCSS-50-22-C	NSCSS-50-22-M	NSCSS-50-22-S	50	22	85	32	M10	576

*1: Hex socket head cap screw is provided.

• Part Number Specification

NSCSS-10-15-C



Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Laser Marking
Please feel free to contact us	Not Available	Not Available	Available / Add'l charge