


SRHFS Hex Socket Flat Head Bolts (with Pin) NEW

[WEB Selection Tool](#)
[WEB CAD Download](#)
[SUS Stainless steel](#)
[Tamper Resistance](#)



● Material/Finish

RoHS2 Compliant

	SRHFS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

- Flat head bolts with pin at the center of their socket.
- This prevents mounting and removing with regular tools.
- Install and remove with **SRH** Dedicated Wrench or **SRHB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.

● Application

Machinery / Tools / Equipment / Devices disassembly prevention / Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

Part Number	M (Coarse)		L										D1	L1	B	Applicable Wrench Type	Applicable Bit Type		Mass (g)	
	Nominal of Thread	Pitch	6	8	10	12	16	20	25	30	35	40					50	Bit		Driver
SRHFS-M3	M3	0.5	6	8	10	12	16	20	25				6	1.75	2	SRH-2	SRHB-2	SRD-6.35	0.53 - 1.4	
SRHFS-M4	M4	0.7		8	10	12	16	20	25	30			8	2.3	2.5	SRH-2.5	SRHB-2.5	SRD-6.35	1.2 - 2.9	
SRHFS-M5	M5	0.8		8	10	12	16	20	25	30	40	50	10	2.8	3	SRH-3	SRHB-3	SRD-6.35	2.3 - 7.4	
SRHFS-M6	M6	1			10	12	16	20	25	30	35	40	50	12	3.4	4	SRH-4	SRHB-4	SRD-6.35	3.9 - 12
SRHFS-M8	M8	1.25			10	12	16	20	25	30	35	40	50	16	4.7	5	SRH-5	SRHB-5	SRD-6.35	9 - 23
SRHFS-M10	M10	1.5								25	30	40		18.3	5.6	6	SRH-6	SRHB-6	SRD-6.35	19 - 29


Part Number	Qty per Pack
SRHFS-M3	10
SRHFS-M4	10
SRHFS-M5	10
SRHFS-M6	10
SRHFS-M8	10
SRHFS-M10	10

● Also sold separately from 1 piece up. → P.xxxx

● **SRH** Dedicated Wrench

Unit : mm


Part Number	B	L1	L2	Mass (g)	Qty per pack
SRH-2	2	50	16	1.8	1
SRH-2.5	2.5	56	18	3.1	1
SRH-3	3	63	20	5	1
SRH-4	4	70	25	10	1
SRH-5	5	80	28	18	1
SRH-6	6	90	32	35	1



● **SRHB** Bit Part No.

Unit : mm


Part Number	B	Mass (g)	Qty per pack
SRHB-2	2	4.81	1
SRHB-2.5	2.5	4.93	1
SRHB-3	3	4.85	1
SRHB-4	4	6.31	1
SRHB-5	5	5.51	1
SRHB-6	6	5.98	1



● **SRD** Dedicated magnet screwdriver


Unit : mm

Part Number	L	B	Mass (g)	Qty per pack
SRD-6.35	210	6.35	98	1



● Part number specification

SRHFS-M5 - 16



Order in number of packs.
Also sold separately from 1 piece up. → P.xxxx

[Individual Sales](#) → P.xxxx
 [Cleanroom Wash & Packaging](#) → P.xxxx
 [Screw Length Adjustment](#) → P.xxxx
 [Vibration Resistant](#) → P.xxxx
 [Modification process for captive use](#) → P.xxxx