


KUM
KUMS

KUF
KUFS



- Flat type knurled knobs.
- A rich variety of thread sizes from M3 to M10 are available.
- There are two types of materials.
 - KUM** **KUF** — Made of steel
 - KUMS** **KUFS** — Made of Stainless Steel
- Materials and types can be selected by a product code.

Product Code	Material	Type
KUM	Made of Steel	Male Screw
KUF	Made of Steel	Female Screw
KUMS	Made of Stainless Steel	Male Screw
KUFS	Made of Stainless Steel	Female Screw

- **KUM** has a round-shaped thread tip to be distinguished from **KUMS**.

• Material/Finish

RoHS2 Compliant

	KUM	KUF	KUMS / KUFS
Main Body	SWCH10R Buffing / Chrome Plating	SUM22L Buffing / Chrome Plating	SUS303*1

*1: For **KUMS-36-M10**, it is SUS304.

Dimensions

KUM **KUMS** Male Screw

Unit : mm

Part Number Made of Steel	Part Number Made of Stainless Steel	D 2	M (Coarse)		H	Mass (g)
			Nominal of Thread 3	Pitch		
KUM-12-M3	KUMS-12-M3	12	M3	0.5	2.5	2 - 4
KUM-16-M4	KUMS-16-M4	16	M4	0.7	3.5	5 - 7
KUM-20-M5	KUMS-20-M5	20	M5	0.8	4	12 - 13
KUM-24-M6	KUMS-24-M6	24	M6	1	5	20 - 25
KUM-30-M8	KUMS-30-M8	30	M8	1.25	6	40 - 46
KUM-36-M10	KUMS-36-M10	36	M10	1.5	8	78 - 90

KUF **KUFS** Female Screw

Unit : mm

Part Number Made of Steel	Part Number Made of Stainless Steel	D 2	M (Coarse)		Lf	A	d	H	Mass (g)
			Nominal of Thread 3	Pitch					
KUF-12-M3	KUFS-12-M3	12	M3	0.5	3	2.5	6	3	2
KUF-16-M4	KUFS-16-M4	16	M4	0.7	4	3.5	8	4	5
KUF-20-M5	KUFS-20-M5	20	M5	0.8	5	4	10	5	10
KUF-24-M6	KUFS-24-M6	24	M6	1	6	5	12	6	18
KUF-30-M8	KUFS-30-M8	30	M8	1.25	8	6	16	8	34
KUF-36-M10	KUFS-36-M10	36	M10	1.5	10	8	20	10	64



KUM **KUF** Made of Steel | **KUMS** **KUFS** Made of Stainless Steel

Part Number Male Screw	Lm (mm) 4							Part Number Female Screw
	6	10	16	20	25	30	40	
KUM-12-M3	●	●	●					KUF-12-M3
KUM-16-M4	●	●	●					KUF-16-M4
KUM-20-M5		●	●	●				KUF-20-M5
KUM-24-M6		●	●	●	●	●		KUF-24-M6
KUM-30-M8			●	●	●	●		KUF-30-M8
KUM-36-M10				●	●	●	●	KUF-36-M10
KUMS-12-M3	●	●	●					KUFS-12-M3
KUMS-16-M4	●	●	●					KUFS-16-M4
KUMS-20-M5		●	●	●				KUFS-20-M5
KUMS-24-M6		●	●	●	●	●		KUFS-24-M6
KUMS-30-M8			●	●	●	●		KUFS-30-M8
KUMS-36-M10				●	●	●	●	KUFS-36-M10

• Related Products

Standard type knurled knobs **KNM** **KNF** **KNMS** **KNFS** are available.
 → P.xxxx



Flat type captive knurled knob **KUM-SC** is available.
 → P.xxxx



• Part number specification

KUM - 24 - M6 - 20

For male screw type, select a **4** thread length Lm from the dimension table.