



- The clamper joints 2 shafts with T-shaped cross.
- Clamping Type. Mounting shaft and removing shaft are easy. Moreover this does not scratch the shaft.
- Space-saving layout is possible.
- Convenient for fixing of side guide and sensors of the conveyance line.
- Light aluminum and stainless steel with highly corrosion-resistant are standardized.
- Compatible with both round shaft and square shaft.
- All products are provided with hex socket head cap screw.

*1: Dimensional allowance before slit machining.

Material/Finish



	FCTS-C
Main body	SUS304
Hex Socket Head Cap Screw	SUSXM7 Molybdenum Disulfide Coating

Unit : mm

Part Number	Mass (g)	D1	D2	B1	A	W	L	H	F1	F2	M (Coarse)
FCTS-8-10-C	111	8	10		22	35	12.5	11	5.5	3.7	M3
FCTS-10-10-C	106	10	10	8	22	35	12.5	11	5.5	3.7	M3
FCTS-12-12-C	154	12	12	10	25	40	14.5	12.5	6	3.8	M3
FCTS-15-15-C	276	15	15	12	30	50	18	15.5	7	4.5	M4
FCTS-20-20-C	553	20	20	16	38	63	21.5	20	9	5.5	M5

- Use a long wrench to tighten the screw.

- Part number specification

FCTS-15-15-C



Cleanroom Wash & Packaging Available / Add'l charge	Screw Length Adjustment Not Available	Vibration Resistant Please feel free to contact us	Laser Marking Available / Add'l charge
--	--	---	---