

- Plastic revolving grip superior in cost effectiveness
- Material/Finish RoHS


	GTR
Grip Part	Nylon 6 (Black)
Thread Part	SS400 Trivalent Chromate Treatment

Unit : mm

Part Number	D <span style="color: red;">❶</span>	M (Coarse)		Lm	d	H	Mass (g)
		Nominal of Thread <span style="color: red;">❷</span>	Pitch				
<b>GTR-18-M5</b>	18	M5	0.8	10	12	50	15
<b>GTR-19-M6</b>	19	M6	1	13	13	65	26
<b>GTR-24-M8</b>	24	M8	1.25	15	17	80	50
<b>GTR-28-M10</b>	28	M10	1.5	20	20	95	86

### ● Installation Method

Insert the spacer ❸ and bolt ❹ into the grip mainbody ❷, set the disc spring ❶ to the mounting surface (refer to the cross section diagram after mounting), and tighten the bolt ❹ with a screwdriver ❺. Then, check the tightening and the rotation of the grip main body, and insert the cap ❺ into the grip main body.



- Part number specification

## GTR-28-M10

Product Code ❶ ❷

Cleanroom Wash & Packaging → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx	Modification of Shaft Hole Diameter → P.xxxx
Not Available	Not Available	Available / Add'l charge	Not Available