HSM Stainless Steel Handwheels

SUS Stainless steel Shaft bore process required



- Standard model with a stainless steel handwheel.
- Products with/without grip mounting holes can be selected by the end symbol of the part number. 2
  HSM ——With grip mounting hole
  HSM-N ——Without grip mounting hole
- There is no grip supplied with this product. Order a grip separately. ➡ P.xxxx

- Material/Finish

RoHS

	HSM
Main body	SCS13 (Equivalent to SUS304)

Unit : mm

Part Number With grip mounting hole	M (Coarse)		P	Part Number Without Grip Mounting Hole	D 1	H	A	s	d	L	E	Number of Spokes	Mass (g)
	Nominal of Thread	Pitch											
HSM-80	M5	0.8	33	**HSM-80-N**	80	28.5	8.5	20	26	17	12	2	260
HSM-100	M5	0.8	43	**HSM-100-N**	100	30.5	8.5	22	26	18	13	2	320
HSM-125	M6	1	54	**HSM-125-N**	125	34.5	8.5	26	32	20	15	2	500
HSM-160	M8	1.25	71	**HSM-160-N**	160	42.8	10.8	32	36	24	18	2	900
HSM-200	M10	1.5	90	**HSM-200-N**	200	43	12	31	42	24	19	2	1300
HSM-250	M10	1.5	113	**HSM-250-N**	250	54	14	40	50	34	20	3	2400

- Recommended applicable grip

Part Number	Recommended applicable grip	
	GSS	GNTRS
HSM-80	GSS-5	GNTRS-18 - M5
HSM-100	GSS-5	GNTRS-18 - M5
HSM-125	GSS-6	GNTRS-19 - M6
HSM-160	GSS-8	GNTRS-24 - M8
HSM-200	GSS-10	GNTRS-28 - M10
HSM-250	GSS-10	GNTRS-28 - M10

- Part number specification

HSM - 80 - N

Product Code 1 2

Cleanroom Wash & Packaging ➡ P.xxxx	Vibration Resistant ➡ P.xxxx	Laser Marking ➡ P.xxxx	Modification of Shaft Hole Diameter ➡ P.xxxx
Available / Add'l charge	Not Available	Available / Add'l charge	Available / Add'l charge