


● Installation example

Make a screw hole in the cover, then pass the knob thread through it. Even when the screw is removed from the frame, the knob does not fall out from the cover because the knob thread catches on the screw hole of the cover.



KUM-SC Captive Knurled Knob

- Captive type knurled knob. Prevents fall-off and loss of the knob.
- Foreign matter entry countermeasures in food processing machinery and so on, as well as CE marking support ().
- Flat type.
- Material/Finish



KUM-SC	
Main body	SWCH10R Buffing / Chrome Plating

⚠ Precautions for Use

Screw hole inner diameter on the cover side shall be at least the d_1 dimension.
The cover thickness should be 0.8 mm or above.

● Part number specification

KUM-24-M6-20-SC

Product Code **1** **2** **3** Captive

For **3** screw length L, select from the sizes marked with ● in the table.

Dimensions

Unit : mm

Part Number	D 1	M (Coarse)		Lm	H	d1	Mass (g)
		Nominal of Thread 2	Pitch				
KUM-12-M3-SC	12	M3	0.5	4	2.5	2.2	2 - 3
KUM-16-M4-SC	16	M4	0.7	5	3.5	3	6
KUM-20-M5-SC	20	M5	0.8	6	4	3.9	11 - 12
KUM-24-M6-SC	24	M6	1	8	5	4.6	20 - 21
KUM-30-M8-SC	30	M8	1.25	10	6	6.3	36 - 40
KUM-36-M10-SC	36	M10	1.5	12	8	8	69 - 77

Part Number	L (mm) 3						
	10	16	20	25	30	40	
KUM-12-M3-SC	●	●					
KUM-16-M4-SC	●	●					
KUM-20-M5-SC	●	●	●				
KUM-24-M6-SC		●	●	●	●		
KUM-30-M8-SC		●	●	●	●		
KUM-36-M10-SC			●	●	●		●

Cleanroom Wash & Packaging → P.0000	Screw Combination → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Laser Marking → P.0000
Not Available	Not Available	Not Available	Not Available	Not Available