



- It has excellent chemical resistance compared to metal screws.
- The end face of the screw thread is covered, increasing designability and safety.
- The properties and precautions of plastic screws
➔ P.xxxx

● Application

General industrial machines / Food industry machines / Medical equipment / Audio equipment / Safety measures

● Material/Finish



	SPO-CN
Main Body	POM (Polyacetal)
Heat Resistance Temperature*1	95°C

*1 : This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

Unit : mm

Part Number ◀1	M (Coarse)		Lf	B	T*2	Mass (g)	Qty*1 per Pack
	Nominal of Thread	Pitch					
SPO-M3-CN	M3	0.5	3	5.5	5.4	0.10	10
SPO-M4-CN	M4	0.7	4	7	6.2	0.19	10
SPO-M5-CN	M5	0.8	7	8	11	0.39	10
SPO-M6-CN	M6	1	9	10	12	0.74	10
SPO-M8-CN	M8	1.25	6	13	15	1.9	10

*1 : Also sold separately from 1 piece up. ➔ P.xxxx

*2 : M5/M6/M8 are JIS1, M4 is JIS3, and M3 is an original standard.

● Part number specification

SPO-M3-CN



Select the part number and order by number of packs.
Also sold separately from 1 piece up. ➔ P.xxxx

Individual Sales ➔ P.xxxx	Cleanroom Wash & Packaging ➔ P.xxxx	Screw Length Adjustment ➔ P.xxxx	Vibration Resistant ➔ P.xxxx	Modification process for captive use ➔ P.xxxx
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available