




SPO-YN Plastic Screws - Wing Nuts - POM **NEW**

WEB Selection Tool

WEB CAD Download



- It has excellent chemical resistance compared to metal screws.
- It can be installed/removed without the use of tools.
- The properties and precautions of plastic screws
→ P.xxxx
- Application

General industrial machines / Food industry machines / Medical equipment / Audio equipment

• Material/Finish

RoHS2 Compliant

	SPO-YN
Main Body	POM (Polyacetal)
Heat Resistance Temperature*1	95°C

*1 : This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

Unit : mm

Part Number	M (Coarse)		D1	H	A	Mass (g)	Qty*1 per Pack
	Nominal of Thread	Pitch					
SPO-M4-YN	M4	0.7	20	10	8	0.39	10
SPO-M5-YN	M5	0.8	25	12	10	0.68	10
SPO-M6-YN	M6	1	32	16	12	1.4	10
SPO-M8-YN	M8	1.25	40	20	16	2.9	10

*1 : Also sold separately from 1 piece up. → P.xxxx

• Part number specification

SPO-M4-YN



Select the part number and order by number of packs.
Also sold separately from 1 piece up. → P.xxxx

Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available