





SPVC-N



SPVC-W



Material/Finish



SPVC-N / SPVC-W

Main body	H-PVC(Hard Polyvinyl Chloride)
Heat Resistance Temperature*1	35°C

*1: This is the value for the plastic material. The maximum operating temperature of the product changes with performance conditions such as tightening torque.

Notice on Product Discontinuation and Launch of Successor Products

H-PVC plastic screws will be discontinued as of the last order on Monday, January 24, 2022.

With some exceptions, the successor products (new products) will be released on Tuesday, January 25, 2022.

For details, refer to

https://www.nbk1560.com/news/2021/20210512_H-PVC_SPVC/.



- These products have excellent chemical resistance against strong acids and organic solvents as well as halogen compounds such as hydrogen sulfide and bromine.
- They can be used in atmospheres in which metal and PVC (polyvinyl chloride) cannot be used.
- Max. Operating Temperature*1 (min./max.): -10/35 deg C
- Two colors, ivory and gray, are available.
- | | | |
|-----------|------|-------|
| IV | ———— | Ivory |
| GR | ———— | Gray |
- The properties and precautions of plastic screws
→ P.xxxx

Application

FPD production equipment, semiconductor devices, printed circuit board etching devices, metallic surface treatment equipment and facilities, and chemical plants

SPVC-N Hex Nuts

Unit : mm

Part Number	M (Coarse)		B	T	Mass (g)	Qty per pack
	Nominal of Thread	Pitch				
SPVC-M4-N	M4	0.7	7	3.2	0.14	1
SPVC-M5-N	M5	0.8	8	4.7	0.24	1
SPVC-M6-N	M6	1	10	5.2	0.44	1


SPVC-W Washers

Unit : mm

Part Number	d	D	t	Nominal	Mass (g)	Qty per pack
SPVC-4-W	4.3	9	0.8	4	0.053	1
SPVC-5-W	5.3	10	1	5	0.077	1
SPVC-6-W	6.4	12.5	1.6	6	0.2	1

Part number specification

SPVC-M5-N-IV



Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
1 pc. in 1 bag	Available / Add'l charge	Not Available	Not Available	Not Available