

- For work and jig locating and centering, etc.
- Please combine with the block **SAK-A** **SAK-B**.
- Adjust bolt **SAT** and block **SAK-A** **SAK-B** combination

Part Number	Blocks for applicable adjust bolt	
<b>SAT-M6</b>	<b>SAK-6-A</b>	<b>SAK-6-B</b>
<b>SAT-M8</b>	<b>SAK-8-A</b>	<b>SAK-8-B</b>
<b>SAT-M10</b>	<b>SAK-10-A</b>	<b>SAK-10-B</b>
<b>SAT-M12</b>	<b>SAK-12-A</b>	<b>SAK-12-B</b>

### Material/Finish




	<b>SAT</b>
Main body	S45C Nickel Plating

Unit : mm

Part Number	M (Coarse)		L <sup>②</sup>				L4	L1	D2	B	d	L2	Mass (g)		
	Nominal of Thread <sup>①</sup>	Pitch													
<b>SAT-M6</b>	M6	1	20	30	35	40	50	60	4.6	10	8.5	10	5.5	9	14 - 20.5
<b>SAT-M8</b>	M8	1.25	30			40	50	60	6	15	11.5	13	7.5	12	36 - 48
<b>SAT-M10</b>	M10	1.5	30			40	50	60	7	15	15.5	17	9.5	16	64 - 82
<b>SAT-M12</b>	M12	1.75	30			40	50	60	7	20	17.5	19	11.5	19	100 - 125

### Usage example

Usable as a simple positioning mechanism in combination with a Block for Adjust Bolts.



### Part number specification

## SAT - M8 - 40

Product Code <sup>①</sup> <sup>②</sup>

Cleanroom Wash & Packaging Not Available	Screw Combination Not Available	Screw Length Adjustment Available / Add'l charge	Vibration Resistant Available / Add'l charge
---	------------------------------------	---	---