



- Parallel pin for locating.
- Stepped type with different dimensional allowance at both ends.
- Bushing for locating pin **PJA** (→ P.xxxx)
Use it in combination with **PJB** (→ P.xxxx).
- Material/Finish RoHS

	PJP
Main body	SUJ2 (hardness: 58 HRC or above) - Polishing

Unit : mm

Part Number	D ◀1	p ⁶	h ₇	L ◀2	L ₁	L ₂	Mass (g)
PJP-3-10	3	+0.012 +0.006	0 -0.010	10	1	7	0.6
PJP-3-15	3	+0.012 +0.006	0 -0.010	15	1	10	0.8
PJP-3-20	3	+0.012 +0.006	0 -0.010	20	1	13	1.1
PJP-4-10	4	+0.020 +0.012	0 -0.012	10	1.5	7	1
PJP-4-15	4	+0.020 +0.012	0 -0.012	15	1.5	10	1.5
PJP-4-20	4	+0.020 +0.012	0 -0.012	20	1.5	13	2
PJP-5-10	5	+0.020 +0.012	0 -0.012	10	1.5	7	1.6
PJP-5-15	5	+0.020 +0.012	0 -0.012	15	1.5	10	2.4
PJP-5-18	5	+0.020 +0.012	0 -0.012	18	1.5	12	2.8
PJP-5-20	5	+0.020 +0.012	0 -0.012	20	1.5	13	3.1
PJP-6-10	6	+0.020 +0.012	0 -0.012	10	1.5	7	2.3
PJP-6-15	6	+0.020 +0.012	0 -0.012	15	1.5	10	3.4
PJP-6-18	6	+0.020 +0.012	0 -0.012	18	1.5	12	4.1
PJP-6-20	6	+0.020 +0.012	0 -0.012	20	1.5	13	4.5
PJP-8-20	8	+0.024 +0.015	0 -0.015	20	2	13	8
PJP-8-25	8	+0.024 +0.015	0 -0.015	25	2	16	10
PJP-8-30	8	+0.024 +0.015	0 -0.015	30	2	19	12
PJP-10-25	10	+0.024 +0.015	0 -0.015	25	2	16	16
PJP-10-30	10	+0.024 +0.015	0 -0.015	30	2	19	19
PJP-12-40	12	+0.029 +0.018	0 -0.018	40	2	25	36

- Part number specification

PJP-5-15

Product Code ◀1 ◀2

Cleanroom Wash & Packaging → P.xxxx Not Available	Vibration Resistant → P.xxxx Not Available	Laser Marking → P.xxxx Not Available
--	---	---