

- Use this as a recipient of the stopper bolt **SSB-A** (→ P.xxxx) **SSB-B** (→ P.xxxx) and stopper screw **SAN-B** (→ P.xxxx).
- The hexagon head end face has already been quenched. It is highly abrasion-resistant.

● Material/Finish




	SPM
Main body	S45C end face quenching (hardness: 35 HRC or above) - Polishing Trivalent Chromate Treatment

Unit : mm

Part Number	M (Coarse)		L3	L1	L	B	C	Mass (g)
	Nominal of Thread	Pitch						
SPM-M3	M3	0.5	7	2	5	6	6.9	0.6
SPM-M4	M4	0.7	8.8	2.8	6	7	8.1	1.3
SPM-M5	M5	0.8	10.5	3.5	7	8	9.2	2.4
SPM-M6	M6	1	12	4	8	10	11.5	4.5
SPM-M8	M8	1.25	15	5	10	13	15	9.5
SPM-M10	M10	1.5	20	6	14	17	19.6	20
SPM-M12	M12	1.75	23	7	16	19	21.9	31

● Usage example

In combination with a stopper screw **SAN-B**.



● Part number specification

SPM-M10

Product Code

Cleanroom Wash & Packaging → P.xxxx	Screw Combination → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx
Not Available	Not Available	Not Available	Available / Add'l charge