

● Material/Finish



	<b>SCS-F-R</b>
Thread Part	SCM435 Ferrosferric Oxide Film (Black)
Ball	SUJ2 (Hardness: 62 - 67 HRC)


- Clamping screw of the fine screw threaded type for easy fine adjustment of threading amount.
- Point contact by full ball securely fixes a work.
- For tool holder set screw, pressure piece and stopper.
- We also produce products of special specifications, e.g. nominal diameter of thread, length and surface treatment. Please feel free to contact our customer service.

Unit : mm

Part Number	M (Fine)		L	D	B	Max. Allowable load (N)	Mass (g)
	Nominal of Thread	Pitch					
<b>SCS-M6F-10-R</b>	M6	0.75	10.8	4	3	9000	1.5
<b>SCS-M6F-16-R</b>	M6	0.75	16.8	4	3	9000	2.5
<b>SCS-M6F-20-R</b>	M6	0.75	20.8	4	3	9000	3.4
<b>SCS-M6F-25-R</b>	M6	0.75	25.8	4	3	9000	4
<b>SCS-M8F-12-R</b>	M8	1	13.2	5.56	4	15000	3.2
<b>SCS-M8F-20-R</b>	M8	1	21.2	5.56	4	15000	5.7
<b>SCS-M8F-25-R</b>	M8	1	26.2	5.56	4	15000	7.7
<b>SCS-M8F-30-R</b>	M8	1	31.2	5.56	4	15000	9
<b>SCS-M10F-16-R</b>	M10	1	17.7	7	5	24000	7
<b>SCS-M10F-20-R</b>	M10	1	21.7	7	5	24000	9.5
<b>SCS-M10F-25-R</b>	M10	1	26.7	7	5	24000	11
<b>SCS-M10F-35-R</b>	M10	1	36.7	7	5	24000	16
<b>SCS-M12F-20-R</b>	M12	1.5	22	8.5	6	30000	12.5
<b>SCS-M12F-30-R</b>	M12	1.5	32	8.5	6	30000	20
<b>SCS-M12F-40-R</b>	M12	1.5	42	8.5	6	30000	28

● Usage example

For fixing of works that are easily scratched.



● Part Number Specification

**SCS-M6F-25-R**



Cleanroom Wash & Packaging → P.0000	Screw Combination → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000
Not Available	Not Available	Not Available	Available / Add'l charge