




SRWFS Triwing Flat Head Machine Screws

Tamper Resistance **SUS** Stainless steel



● Material/Finish



	SRWFS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

- This prevents mounting and removing with regular tools.
- Install and remove with **SRWB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.

● Application

Machinery / Tools / Equipment / Devices disassembly prevention/ Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

Unit : mm

Part Number	M (Coarse)		L										D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)	Qty per Pack	
	Nominal of Thread	Pitch	5	6	8														
SRWFS-M2	M2	0.4	5	6	8									3.8	1.2	SRWB-1	SRD-6.35	0.16 - 0.21	10
SRWFS-M3	M3	0.5	6	8	10	12	16	20	25					5.5	1.65	SRWB-2	SRD-6.35	0.53 - 1.4	10
SRWFS-M4	M4	0.7	6	8	10	12	16	20	25	30				8.4	2.7	SRWB-4	SRD-6.35	1.1 - 2.9	10
SRWFS-M5	M5	0.8			10	12	16	20	25	30	40	50		9.3	2.7	SRWB-5	SRD-6.35	2.5 - 7.4	10
SRWFS-M6	M6	1			10	12	16	20	25	30	40	50		11.3	3.3	SRWB-6	SRD-6.35	3.9 - 12	10
SRWFS-M8	M8	1.25					16	20	25	30	40	50		15.8	4.65	SRWB-7	SRD-6.35	11 - 23	10

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● **SRWB** Dedicated bit

Unit : mm

Part Number	L	B	Mass (g)
SRWB-1	25.4	6.35	4.7
SRWB-2	25.4	6.35	4.8
SRWB-4	25.4	6.35	5.2
SRWB-5	25.4	6.35	5.6
SRWB-6	25.4	6.35	6.2
SRWB-7	25.4	6.35	6.6

SRWB




● **SRD** Dedicated magnet screwdriver

Unit : mm

Part Number	L	B	Mass (g)
SRD-6.35	210	6.35	98

SRD



● Part number specification

SRWFS-M5-16



Individual Sales → P.0000	Cleanroom Wash & Packaging → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Modification process for captive use → P.0000
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available