


SNSS-TF Hex Socket Head Cap Screws - PTFE Coating




[WEB Selection Tool](#)
[WEB CAD Download](#)
[Seizing Prevention](#)
[Chemical-proof](#)
[SUS Stainless steel](#)



- Tightening property (reference)
Part Number : SNSS-M5 - 25-TF

➔ P.xxxx



- Excellent chemical resistance.
- The coating has excellent lubricating ability and is suitable for prevention of seizing.

● Application

Seizing prevention. FPD production equipment, semiconductor devices, printed circuit board etching devices, metallic surface treatment equipment and facilities, and chemical plants

● Material/Finish

RoHS2 Compliant

	SNSS-TF
Main Body	SUSXM7 (S.S. Grade : A2) PTFE(Polytetrafluoroethylene) Coating
Strength Class	A2-70

Unit : mm

Part Number	M (Coarse)		L ◀2													D1	L1	B	Mass (g)
	Nominal of Thread ◀1	Pitch	5	6	8	10	12	16	20	25	30	35	40						
SNSS-M3-TF	M3	0.5	5	6	8	10	12	16	20						5.5	3	2.5	0.67 - 1.4	
SNSS-M4-TF	M4	0.7		6	8	10	12	16	20	25					7	4	3	1.5 - 3.2	
SNSS-M5-TF	M5	0.8			8	10	12	16	20	25					8.5	5	4	2.5 - 4.8	
SNSS-M6-TF	M6	1				10	12	16	20	25	30				10	6	5	4.7 - 8.3	
SNSS-M8-TF	M8	1.25						16	20	25	30	35			13	8	6	12 - 19	
SNSS-M10-TF	M10	1.5							20	25	30	35	40		16	10	8	23 - 33	

Part Number	Qty per pack
SNSS-M3-TF	1
SNSS-M4-TF	1
SNSS-M5-TF	1
SNSS-M6-TF	1
SNSS-M8-TF	1
SNSS-M10-TF	1

- Part number specification

SNSS - M6 - 25 - TF

Product Code ◀1 ◀2 Product Code

1 Individual Sales ➔ P.xxxx	Cleanroom Wash & Packaging ➔ P.xxxx	Screw Length Adjustment ➔ P.xxxx	Vibration Resistant ➔ P.xxxx	Modification process for captive use ➔ P.xxxx
1 unit in 1 bag	Available / Add'l charge	Not Available	Not Available	Please feel free to contact us