


Structure





• Material/Finish



	DKB	DKB-AA / DKB-PB
Keyboard Holder	AC4C-F Electrostatic Coating	
Clamp	AC4C-F Electrostatic Coating	
Clamping Screw	SWRCH Trivalent Chromate Treatment	
Bracket	-	A6063 Anodized

• Option

- A mouse holder **DKM** is available as an option.
- This may be mounted on either side.



Part Number	Mass (g)
DKM	310

• Material / Finish

	DKM
Mouse Holder	SPCC Cation Painting
Mouse Holder Fixing Knob	Nylon 6



- The keyboard can be completely fixed to the mounting surface.
- By tightening the clamping screw, the keyboard is securely fixed and prevented from falling.
- B5 size laptops and 500 mm wide keyboards can be equipped.
- Three types of Mounting System for Display® are available for different types of mounting surfaces.



- For aluminum frame / For wall panel and sheet metal — **DKB**
- For aluminum frame end surface mounting — **DKB-AA**
- For Round Pipe — **DKB-PB**

- Clamp screws of two sizes (Phillips cross recessed pan head machine screws) are supplied.
M6 × 40: Used when the keyboard width is 256 mm to 280 mm.
M6 × 140: Used when the keyboard width is 280 mm to 500 mm.

• Application

Machine tool / Medical equipment / FPD production device / Semiconductor manufacturing device / Packing machine / Food machinery

• Related Products

Fixed type keyboard mounting system **DKBR** is available.
→ P.xxxx



• Part number specification

DKB-500-AA-40

Product Code **1 2**


Example of part number: DKB-500 / DKB-500-PB-42.7

- For aluminum frame / For wall panel and sheet metal

DKB



• Mounting hole details



Part Number	Mass (g)
DKB-500	800

- For aluminum frame end surface mounting

DKB-AA



Part Number	B	Mass (g)	Unit : mm
DKB-500-AA-40	40	970	

- Hex socket low head bolts (M8 × 16 mm) are supplied.

- For Round Pipe

DKB-PB



Part Number	D	L1	L	Mass (g)	Unit : mm
DKB-500-PB-**	28	174	198	1130	
	30			1130	
	34			1120	
	40	1110			
	42.7	178	206	1105	

- Fixing rubber sheet is attached. Dimensional allowance of available round pipe is ±0.5 mm.

