



● Material/Finish



	SM
Main body	SUM22 Chrome Plating

Unit : mm

Part Number	D	M (Coarse)		Lm	d	H	h	h ₁	Mass (g)
		Nominal of Thread	Pitch						
SM-4	10	M4	0.7	9	7	32	28	4	10
SM-5	13	M5	0.8	10	8	40	35	5	25
SM-6	16	M6	1	13	10	50	43	7	45
SM-8	20	M8	1.25	15	13	64	56	8	90
SM-10	25	M10	1.5	18	16	80	70	10	180
SM-12	32	M12	1.75	20	20	100	87	13	350
SM-16	36	M16	2	22	22	112	98	14	500

● Part number specification

SM-4



Cleanroom Wash & Packaging → P.0000	Vibration Resistant → P.0000	Laser Marking → P.0000	Modification of Shaft Hole Diameter → P.0000
Not Available	Available / Add'l charge	Not Available	Not Available