

- Use it in combination with a grip.
- There are two types of materials. ◀1
  - LGS** ——— Made of steel
  - LGSS** ——— Made of stainless steel

- Material/Finish 🌱 RoHS2 Compliant

	LGS	LGSS
Main body	Steel Matte Chrome Plating	SUS303


### ● Recommended Knobs & Grips

Part Number Made of Steel	Part Number Made of Stainless Steel	Recommended Knobs & Grips					
		<b>PB</b> → P.xxxx	<b>PC</b> → P.xxxx	<b>KDC</b> → P.xxxx	<b>KEC</b> → P.xxxx	<b>GTF</b> → P.xxxx	<b>GTF5</b> → P.xxxx
<b>LGS-M6</b>	<b>LGSS-M6</b>	<b>PB-20×M6</b>	<b>PC-20×M6</b>	<b>KDC-6</b>	<b>KEC-6</b>	<b>GTF-19×M6</b>	<b>GTF5-19×M6</b>
<b>LGS-M8</b>	<b>LGSS-M8</b>	<b>PB-25×M8</b>	<b>PC-25×M8</b>	<b>KDC-8</b>	<b>KEC-8</b>	<b>GTF-24×M8</b>	<b>GTF5-24×M8</b>
<b>LGS-M10</b>	<b>LGSS-M10</b>	<b>PB-30×M10</b>	<b>PC-30×M10</b>	<b>KDC-10</b>		<b>GTF-24×M10</b>	<b>GTF5-24×M10</b>
<b>LGS-M12</b>	<b>LGSS-M12</b>	<b>PB-40×M12</b>	<b>PC-40×M12</b>			<b>GTF-28×M12</b>	

Unit : mm

Part Number Steel	Part Number Stainless steel	M (Coarse)		L1 <span style="color:red">◀3</span>	A	Lm1	Lm2	Mass (g)
		Nominal of Thread <span style="color:red">◀2</span>	Pitch					
<b>LGS-M6-40</b>	<b>LGSS-M6-40</b>	M6	1	40	8	12	9	20
<b>LGS-M6-60</b>	<b>LGSS-M6-60</b>	M6	1	60	8	12	9	28
<b>LGS-M6-80</b>	<b>LGSS-M6-80</b>	M6	1	80	8	12	9	36
<b>LGS-M8-50</b>	<b>LGSS-M8-50</b>	M8	1.25	50	10	20	11	42
<b>LGS-M8-75</b>	<b>LGSS-M8-75</b>	M8	1.25	75	10	20	11	58
<b>LGS-M8-100</b>	<b>LGSS-M8-100</b>	M8	1.25	100	10	20	11	73
<b>LGS-M10-60</b>	<b>LGSS-M10-60</b>	M10	1.5	60	12	25	14	76
<b>LGS-M10-90</b>	<b>LGSS-M10-90</b>	M10	1.5	90	12	25	14	103
<b>LGS-M10-120</b>	<b>LGSS-M10-120</b>	M10	1.5	120	12	25	14	130
<b>LGS-M12-80</b>	<b>LGSS-M12-80</b>	M12	1.75	80	14	30	14	134
<b>LGS-M12-120</b>	<b>LGSS-M12-120</b>	M12	1.75	120	14	30	14	182
<b>LGS-M12-160</b>	<b>LGSS-M12-160</b>	M12	1.75	160	14	30	14	230

- Usage example  
In combination with a grip.



- Part number specification

**LGSS-M6-40**

1   
 2   
 3

Cleanroom Wash & Packaging → P.xxxx	Screw Combination → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx
S.S. only/ Add'l charge	Not Available	Not Available	Available / Add'l charge	Not Available