



**HSM-AHC** + **GNTRS**

- Standard model with a stainless steel handwheel.
- Products with/without grip mounting holes can be selected by the end symbol of the part number.
- **HSM** — With grip mounting hole
- **HSM-N** — Without grip mounting hole
- There is no grip supplied with this product. Order a grip separately.  $\rightarrow$  P.xxxx

• Material/Finish

HSM	
Main body	SCS13 (Equivalent to SUS304)

Part Number With grip mounting hole	M (Coarse)		P	Part Number Without Grip Mounting Hole	D	H	A	s	d	L	E	Number of Spokes	Mass (g)
	Nominal of Thread	Pitch											
<b>HSM-80</b>	M5	0.8	33	<b>HSM-80-N</b>	80	28.5	8.5	20	26	17	12	2	260
<b>HSM-100</b>	M5	0.8	43	<b>HSM-100-N</b>	100	30.5	8.5	22	26	18	13	2	320
<b>HSM-125</b>	M6	1	54	<b>HSM-125-N</b>	125	34.5	8.5	26	32	20	15	2	500
<b>HSM-160</b>	M8	1.25	71	<b>HSM-160-N</b>	160	42.8	10.8	32	36	24	18	2	900
<b>HSM-200</b>	M10	1.5	90	<b>HSM-200-N</b>	200	43	12	31	42	24	19	2	1300
<b>HSM-250</b>	M10	1.5	113	<b>HSM-250-N</b>	250	54	14	40	50	34	20	3	2400

• Recommended applicable grip

Part Number	Recommended applicable grip	
	<b>GSS</b>	<b>GNTRS</b>
<b>HSM-80</b>	GSS-5	GNTRS-18 - M5
<b>HSM-100</b>	GSS-5	GNTRS-18 - M5
<b>HSM-125</b>	GSS-6	GNTRS-19 - M6
<b>HSM-160</b>	GSS-8	GNTRS-24 - M8
<b>HSM-200</b>	GSS-10	GNTRS-28 - M10
<b>HSM-250</b>	GSS-10	GNTRS-28 - M10

• Part number specification

**HSM-80-N**

Product Code

Cleanroom Wash & Packaging $\rightarrow$ P.xxxx	Vibration Resistant $\rightarrow$ P.xxxx	Laser Marking $\rightarrow$ P.xxxx	Modification of Shaft Hole Diameter $\rightarrow$ P.xxxx
Please feel free to contact us	Not Available	Available / Add'l charge	Available / Add'l charge