




SPC-H Plastic Screws - Hex Head Screws - PC



- PC (polycarbonate) has the highest shock resistance of engineering plastics.
- Max. Operating Temperature*1(min./max.): -40/115°C
- PC has low water absorbency and excellent weather resistance.
- The properties and precautions of plastic screws → P.xxxx

• Application

Electrical and electronic equipment and automobiles

• Material/Finish



SPC-H	
Main Body	PC (Polycarbonate) (Transparent)
Heat Resistance Temperature*1	115°C

*1: This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

Unit : mm

Part Number	M (Coarse)		L	B	L1	Tension Rupture Load*1 (N)	Torsional Torque*1 (N·m)	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch							
SPC-M4-H	M4	0.7	10 12 15 20 25	7	2.8	481	0.39	0.26 - 0.48	50
SPC-M5-H	M5	0.8	10 12 15 20 25 30 35	8	3.5	797	0.8	0.43 - 0.99	50
SPC-M6-H	M6	1	10 12 15 20 25 30 35 40	10	4	1136	1.2	0.69 - 1.7	20
SPC-M8-H	M8	1.25	10 12 15 20 25 30	13	5.5	2088	3.2	1.5 - 2.6	10

*1: Values in chart are for reference only. They are not guaranteed values. The recommended tightening torque is 50% of the torsional torque.

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

• Part number specification

SPC-M5-20-H

Product Code	1	2	Product Code
--------------	---	---	--------------

Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available	Please feel free to contact us