

Thickness: approximately 0.55 mm

- **FSP** (Background color: Silver) Multiples of 0 and 50 are red.
- **FSP-BK** (Background color: Black) All numbers are silver.

• Material/Finish



	FSP
Main Body	SUS304

- Horizontal scale plate. Has adhesive tape to enable use simply by sticking to existing machinery and equipment.
- Convenient for conveyor line shaft adjustment or slide table positioning.
- Standardized 50/100/150/200 mm scale length.
- Made of stainless steel. It has excellent corrosion resistance.
- Corners are rounded. Doesn't come off easily.
- There are 3 types of scales. They can be selected by the symbol of the part number.

Symbol	Scale
<b>R</b>	Zero Point on the Left
<b>L</b>	Zero Point on the Right
<b>C</b>	Center Distribution

- There are two color variations available. They can be selected by the end symbol of the part number.

End Symbol	Background Color	Scale / Numbers
<b>No</b>	Silver	Red/Black
<b>BK</b>	Black	Silver


**FSP** Background color: Silver **FSP-BK** Background color: Black

Unit : mm

Part Number	L1	L	Mass (g)
FSP-50-R	50	58	2.6
FSP-100-R	100	108	4.8
FSP-150-R	150	158	7
FSP-200-R	200	208	9.2
FSP-50-L	50	58	2.6
FSP-100-L	100	108	4.8
FSP-150-L	150	158	7
FSP-200-L	200	208	9.2
FSP-50-C	50	58	2.6
FSP-100-C	100	108	4.8
FSP-150-C	150	158	7
FSP-200-C	200	208	9.2
FSP-50-R-BK	50	58	2.6
FSP-100-R-BK	100	108	4.8
FSP-150-R-BK	150	158	7
FSP-200-R-BK	200	208	9.2
FSP-50-L-BK	50	58	2.6
FSP-100-L-BK	100	108	4.8
FSP-150-L-BK	150	158	7
FSP-200-L-BK	200	208	9.2
FSP-50-C-BK	50	58	2.6
FSP-100-C-BK	100	108	4.8
FSP-150-C-BK	150	158	7
FSP-200-C-BK	200	208	9.2

**⚠ Precautions for Use**

- Use the scale of the **FSP** Scale Plate as a general guideline.
- Thoroughly remove oil and dust on the sticking surface before sticking.



**• Related Products**

Point Lens **FLE**, which is useful to read the scale, is available.

➔ P.xxxx



**FSP-K** models that are the same shape as **FSP** but with mounting holes included are available.

➔ P.xxxx



- Part number specification

**FSP-200-R-BK**

