

Thickness: approximately 0.55 mm

- **FSP-V** (Background color: Silver) Multiples of 0 and 50 are red.
- **FSP-V-BK** (Background color: Black) All numbers are silver.

• Material/Finish



	FSP-V
Main Body	SUS304

FSP-V Background color: Silver **FSP-V-BK** Background color: Black

Unit : mm

Part Number	L1	L	Mass (g)
FSP-50V-T	50	58	2.6
FSP-100V-T	100	108	4.8
FSP-150V-T	150	158	7
FSP-200V-T	200	208	9.2
FSP-50V-B	50	58	2.6
FSP-100V-B	100	108	4.8
FSP-150V-B	150	158	7
FSP-200V-B	200	208	9.2
FSP-50V-C	50	58	2.6
FSP-100V-C	100	108	4.8
FSP-150V-C	150	158	7
FSP-200V-C	200	208	9.2
FSP-50V-T-BK	50	58	2.6
FSP-100V-T-BK	100	108	4.8
FSP-150V-T-BK	150	158	7
FSP-200V-T-BK	200	208	9.2
FSP-50V-B-BK	50	58	2.6
FSP-100V-B-BK	100	108	4.8
FSP-150V-B-BK	150	158	7
FSP-200V-B-BK	200	208	9.2
FSP-50V-C-BK	50	58	2.6
FSP-100V-C-BK	100	108	4.8
FSP-150V-C-BK	150	158	7
FSP-200V-C-BK	200	208	9.2

- Vertical scale plate. Has adhesive tape to enable use simply by sticking to existing machinery and equipment.
- Convenient for conveyor line shaft adjustment or slide table positioning.
- Standardized 50/100/150/200 mm scale length.
- Made of stainless steel. It has excellent corrosion resistance.
- Corners are rounded. Doesn't come off easily.
- There are 3 types of scales. They can be selected by the symbol of the part number.


Symbol	Scale
T	Zero Point at the Bottom
B	Zero Point at the Top
C	Center Distribution

- There are two color variations available. They can be selected by the end symbol of the part number.

End Symbol	Background Color	Scale / Numbers
No	Silver	Red/Black
BK	Black	Silver

⚠ Precautions for Use

- Use the scale of the **FSP-V** Scale Plate as a general guideline.
- Thoroughly remove oil and dust on the sticking surface before sticking.
- Avoid use in high-temperature/high-humidity environments, and do not leave moisture or oil adhered to the product. The scale part may peel off.



• Related Products

Point Lens **FLE**, which is useful to read the scale, is available.



- Part number specification

FSP-200V-T-BK

