


SNSS-MO Hex Socket Head Cap Screws - MoS₂ Coating




[WEB Selection Tool](#)
 [WEB CAD Download](#)
 [Seizing Prevention](#)
 [SUS Stainless steel](#)



- Tightening property (reference)
Part Number : SNSS-M5 - 25-MO

➔ P.xxxx



- Excellent corrosion resistance and abrasion resistance.
- The coating has excellent lubricating ability and is intended to prevent seizing of screws.

● Application

Seizing prevention
FPD production equipment, semiconductor devices,
and general industrial machines

● Material/Finish



	SNSS-MO
Main Body	SUSXM7 (Equivalent to SUS304) Molybdenum Disulfide Coating
Strength Class	A2-70

Unit : mm

Part Number	M (Coarse)		L												D1	L1	B	Mass (g)
	Nominal of Thread	Pitch	5	6	8	10	12	16	20	25	30	35	40					
SNSS-M3-MO	M3	0.5	5	6	8	10	12	16	20						5.5	3	2.5	0.67 - 1.4
SNSS-M4-MO	M4	0.7		6	8	10	12	16	20	25					7	4	3	1.5 - 3.2
SNSS-M5-MO	M5	0.8			8	10	12	16	20	25					8.5	5	4	2.5 - 4.8
SNSS-M6-MO	M6	1				10	12	16	20	25	30				10	6	5	4.7 - 8.3
SNSS-M8-MO	M8	1.25							16	20	25	30	35		13	8	6	12 - 19
SNSS-M10-MO	M10	1.5								20	25	30	35	40	16	10	8	23 - 33

Part Number	Qty*1 per pack
SNSS-M3-MO	10
SNSS-M4-MO	10
SNSS-M5-MO	10
SNSS-M6-MO	10
SNSS-M8-MO	10
SNSS-M10-MO	10

*1 : Also sold separately from 1 piece up. ➔ P.xxxx

● Part number specification

SNSS-M5-16-MO

Product Code **1** **2** Product Code

Order in number of packs.

Also sold separately from 1 piece up. ➔ P.xxxx

Individual Sales ➔ P.xxxx	Cleanroom Wash & Packaging ➔ P.xxxx	Screw Length Adjustment ➔ P.xxxx	Vibration Resistant ➔ P.xxxx	Modification process for captive use ➔ P.xxxx
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Please feel free to contact us