



Thickness: approximately 0.3 mm

- Multiples of 0 and 50 are red.

- Material/Finish



FST-V	
Main body	Polyester (transparent)

- Sticker type vertical scale. Use by sticking to machinery and equipment.
- Standardized 100/200/300 mm scale length.
- Made of flexible polyester. Can be stuck to the curved surfaces of posts or shafts, plus can be cut to a desired length for use.
- Corners are rounded. Doesn't come off easily.
- There are 3 types of scales. They can be selected by the symbol of the part number.

Symbol	Scale
T	Zero point at the bottom
B	Zero point at the top
C	Center distribution

⚠ Precautions for Use

- **FST-V** Use the scale of the Scale Sticker as a general guideline.
- Thoroughly remove oil and dust on the sticking surface before sticking.

- Usage example

In combination with the Cross Clamper **FCCA-C**

FCCS-C (➔ P.xxxx) and the Clamp Lever.



Part Number	L1	L	Mass (g)
FST-100V-T	100	108	0.5
FST-200V-T	200	208	1
FST-300V-T	300	308	1.5
FST-100V-B	100	108	0.5
FST-200V-B	200	208	1
FST-300V-B	300	308	1.5
FST-100V-C	100	108	0.5
FST-200V-C	200	208	1
FST-300V-C	300	308	1.5

Unit : mm

Scale Plate / Scale sticker Length Adjustment ➔ P.xxxx

Available / Add'l charge

• Related Products

Point Lens **FLE**, which is useful to read the scale, is available.

➔ P.xxxx



- Part number specification

FST-200V-T

