


SNSL-PN Hex Socket Head Cap Screws - SUS316L / Surface hardening treatment



Seizing Prevention Heat-resistance



⚠ Precautions for Use

May have lower corrosion resistance than general SUS316L.

We recommend performing a test under the same usage conditions as in actual usage in advance.



- Hardening the screw surface prevents screw seizing / sticking.
- Unlike platings or coatings, there is nothing adhering to the surface, eliminating concerns about contamination due to stripping during tightening.
- Suitable for preventing seizing and sticking in environments where lubricant cannot be used.
- Conforms to JIS B 1176, ISO 4762, and DIN 912.
⇒ Technical Information : JIS B 1176, ISO 4762

● Application

Seizing & Sticking Prevention
FPD production devices / semiconductor production devices / food machinery / general industry machinery

● Material/Finish



SNSL-PN	
Main body	SUS316L Surface hardening treatment
Strength Class	A4-70

Unit : mm

Part Number	M (Coarse)		L													D1	L1	B	Mass (g)	
	Nominal of Thread	Pitch	6	8	10	12	16	20	25	30	35	13	8	6	12					-19
SNSL-M3-PN	M3	0.5															5.5	3	2.5	0.71 - 0.96
SNSL-M4-PN	M4	0.7															7	4	3	1.7 - 2.7
SNSL-M5-PN	M5	0.8															8.5	5	4	2.5 - 4
SNSL-M6-PN	M6	1															10	6	5	4.7 - 8.3
SNSL-M8-PN	M8	1.25															13	8	6	12 - 19

● Part number specification

SNSL - M5 - 16 - PN

Product Code Product Code

Individual Sales → P.0000	Cleanroom Wash & Packaging → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Modification process for captive use → P.0000
1 piece in 1 pack	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Please feel free to contact us