




# SRTS Two - Hole Pan Head Machine Screws

Tamper Resistance **SUS** Stainless steel



● Material/Finish



	<b>SRTS</b>
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

- This prevents mounting and removing with regular tools.
- Install and remove with **SRTB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.
- The simple head design is also suitable for decoration.

● Application

Equipment/devices disassembly/tampering prevention  
 Theft prevention for outdoor facilities  
 Security measures  
 Safety measures

Unit : mm

Part Number <b>1</b>	M (Coarse)		L <b>2</b>							D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch													
<b>SRTS-M3</b>	M3	0.5	6	8	10					6	1.8	SRTB-4	SRD-6.35	0.66 - 0.82	20
<b>SRTS-M4</b>	M4	0.7			10	12	16			8	2.4	SRTB-8	SRD-6.35	1.7 - 2.2	20
<b>SRTS-M5</b>	M5	0.8				12	16	20		10	3	SRTB-10	SRD-6.35	3.4 - 4.3	20

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Related Products

**SRTB** dedicated bits are available.



Dedicated magnetic screwdrivers **SRD** are available.



● Part Number Specification

**SRTS-M5-16**



<b>1</b> Individual Sales Available / Add'l charge	<b>2</b> Cleanroom Wash & Packaging Available / Add'l charge	<b>3</b> Screw Length Adjustment Available / Add'l charge	<b>4</b> Vibration Resistant Available / Add'l charge	<b>5</b> Modification process for captive use Available / Add'l charge
---	---	--	--	---