

● Material/Finish




	NSBFH
Main Body	S45C Head End Face Quenching (Hardness: 35 HRC or Above) Electroless Nickel Plating
Lock Nut	SUS304

- Fine screw thread stopper bolts. Fine adjustment of the screw-in depth is easy.
- Head end face is quenched. It has excellent wear resistance.
- All products are provided with a lock nut.
- Use in combination with the Stoppers for Linear Guides for Positioning series is possible.

Unit : mm

Part Number	M (Fine)		L	H	K	S	F	E	T	Mass (g)
	Nominal of Thread	Pitch								
NSBFH-6-40	M6	0.75	40	4	4	10	8	11.5	5	12.9
NSBFH-6-50	M6	0.75	50	4	4	10	8	11.5	5	14
NSBFH-6-60	M6	0.75	60	4	4	10	8	11.5	5	15.9
NSBFH-8-40	M8	1.0	40	5.5	5.5	13	10	15	6.5	24.3
NSBFH-8-50	M8	1.0	50	5.5	5.5	13	10	15	6.5	27.7
NSBFH-8-60	M8	1.0	60	5.5	5.5	13	10	15	6.5	31.2

● Usage Example



- Use the lock nut on the opposite side of the side that receives the force.

● Part Number Specification

NSBFH-8-50



Cleanroom Wash & Packaging	Screw Combination	Screw Length Adjustment	Vibration Resistant	Laser Marking
Not Available	Not Available	Not Available	Not Available	Not Available