


SPA-H Plastic Hex Head Screws - RENY

High strength Lightweight High Specific Strength



Material/Finish



SPA-H	
Main Body	RENY™*1 (50% Glass Fiber Reinforced Polyamide MXD6) (Ivory)
Heat Resistance Temperature*2	105°C

*1: RENY™ is a trademark or registered trademark of Mitsubishi Gas Chemical Company, Inc.

*2: This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

- RENY™ hex head bolts.
- RENY™ is a thermoplastic engineering plastic with excellent tensile and bending strength.
- It is highly fatigue-resistant and has excellent creep and heat insulation properties.
- While it is nearly as strong as metal, its weight is approximately 1/5 of iron.
- For the properties and precautions for use of plastic screws, see "Properties of Plastic Screws."

Application

Heat insulation and dew condensation prevention of refrigerating and freezing facilities
Electrical and electronic equipment / Offshore instruments / Plating facilities

Unit : mm

Part Number ❶	M (Coarse)		B	L1	Lz*1	Tension Rupture Load*2 (N)	Torsional Rupture Torque*2 (N·m)	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch							
SPA-M5-H	M5	0.8	8	3.5	Full Thread	2407	1.65	0.54 - 1.2	20
SPA-M5-H(100)	M5	0.8	8	3.5	Full Thread	2407	1.65	0.54 - 1.2	100
SPA-M5-H(1000)	M5	0.8	8	3.5	Full Thread	2407	1.65	0.54 - 0.64	1000
SPA-M5-H(500)	M5	0.8	8	3.5	Full Thread	2407	1.65	0.72 - 0.85	500
SPA-M5-H(250)	M5	0.8	8	3.5	Full Thread	2407	1.65	0.99 - 1.2	250
SPA-M6-H	M6	1	10	4 (L≤40) 5 (L≥50)	50 (L≥55)	3106	2.74	0.95 - 4.4	10
SPA-M6-H(100)	M6	1	10	4 (L≤40) 5 (L≥50)	50 (L≥55)	3106	2.74	0.95 - 3.7	100
SPA-M6-H(500)	M6	1	10	4 (L≤40) 5 (L≥50)	50 (L≥55)	3106	2.74	0.95 - 1	500
SPA-M6-H(250)	M6	1	10	4 (L≤40) 5 (L≥50)	50 (L≥55)	3106	2.74	1.2 - 1.5	250
SPA-M6-H(200)	M6	1	10	4 (L≤40) 5 (L≥50)	50 (L≥55)	3106	2.74	1.7 - 2.1	200
SPA-M6-H(50)	M6	1	10	4 (L≤40) 5 (L≥50)	50 (L≥55)	3106	2.74	4 - 4.4	50
SPA-M8-H	M8	1.25	13	5.5 (L≤50) 6 (L≥55)	30 (L=50) 50 (L≥55)	5335	6.22	1.9 - 12	10
SPA-M8-H(100)	M8	1.25	13	5.5 (L≤50) 6 (L≥55)	30 (L=50) 50 (L≥55)	5335	6.22	1.9 - 4.1	100
SPA-M8-H(250)	M8	1.25	13	5.5 (L≤50) 6 (L≥55)	30 (L=50) 50 (L≥55)	5335	6.22	1.9	250
SPA-M8-H(200)	M8	1.25	13	5.5 (L≤50) 6 (L≥55)	30 (L=50) 50 (L≥55)	5335	6.22	2.1 - 2.7	200
SPA-M8-H(50)	M8	1.25	13	5.5 (L≤50) 6 (L≥55)	30 (L=50) 50 (L≥55)	5335	6.22	4.8 - 12	50
SPA-M10-H	M10	1.5	17	7 (L≤45) 8 (L≥50)	20 (L=45) 25 (L=50) 50 (L≥60)	7646	11.39	4.1 - 19	5
SPA-M10-H(100)	M10	1.5	17	7 (L≤45) 8 (L≥50)	20 (L=45) 25 (L=50) 50 (L≥60)	7646	11.39	4.1 - 19	100
SPA-M10-H(50)	M10	1.5	17	7 (L≤45) 8 (L≥50)	20 (L=45) 25 (L=50) 50 (L≥60)	7646	11.39	6.1 - 12	50
SPA-M12-H	M12	1.75	19	8 (L≤70) 10 (L≥80)	90 (L≥100)	7511	15.93	7.2 - 33	1
SPA-M12-H(50)	M12	1.75	19	8 (L≤70) 10 (L≥80)	90 (L≥100)	7511	15.93	7.2 - 33	50
SPA-M16-H	M16	2	24	13	50 (L≥55)	19987	38.9	24 - 57	1
SPA-M16-H(50)	M16	2	24	13	50 (L≥55)	19987	38.9	24 - 57	50


*1: If the "L" value is not in parentheses, the screw is full thread.

*2: Values in chart are for reference only. They are not guaranteed values. The recommended tightening torque is 50% of the torsional torque.

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.


Part Number Specification

SPA-M5-30-H



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available



Part Number	L (mm) 																					
	8	10	12	15	20	25	30	35	40	45	50	55	60	65	70	75	80	90	100	120	150	
SPA-M5-H	●	●	●	●	●	●	●	●														
SPA-M5-H(100)	●	●	●	●	●	●	●	●														
SPA-M5-H(1000)	●	●	●																			
SPA-M5-H(500)				●	●																	
SPA-M5-H(250)						●	●	●														
SPA-M6-H		●	●	●	●	●	●	●	●		●	●	●	●	●	●	●	●	●			
SPA-M6-H(100)		●	●	●	●	●	●	●	●		●	●	●	●	●	●	●					
SPA-M6-H(500)		●	●																			
SPA-M6-H(250)				●	●	●																
SPA-M6-H(200)							●	●	●													
SPA-M6-H(50)																		●	●			
SPA-M8-H		●	●	●	●	●	●	●	●		●	●	●	●	●	●	●	●	●	●	●	●
SPA-M8-H(100)		●	●	●	●	●	●	●	●													
SPA-M8-H(250)		●																				
SPA-M8-H(200)			●	●	●																	
SPA-M8-H(50)											●	●	●	●	●	●	●	●	●	●	●	●
SPA-M10-H			●	●	●	●	●	●	●		●		●		●	●	●			●		●
SPA-M10-H(100)			●	●	●	●														●		●
SPA-M10-H(50)							●	●	●	●	●		●		●	●	●					
SPA-M12-H					●	●	●		●	●	●		●		●	●	●			●	●	●
SPA-M12-H(50)					●	●	●		●	●	●		●		●	●	●			●	●	●
SPA-M16-H											●	●	●		●	●	●			●	●	●
SPA-M16-H(50)											●	●	●		●	●	●			●	●	●